DC Bias Current Test System NEW 6210/6220/6240+6632

Features

- Current and frequency graphic scanning analysis
- Temperature-rising scan function can solve the problems of overheating a DUT to burn
- DCR Measurement function
- Long-term consecutive maximum power output
- Interchangeable bi-direction current function
- Up to 6 units of the 6210/6220 DC Current Source Series can be overlapped to provide a maximum voltage of 20Vdc, maximum power output 25W, Scalable current output up to 120A
- Up to 8 units of the 6240 DC Current Source Series can be overlapped to provide a maximum voltage of 12Vdc, maximum power output 50W
- Direct Handler interfaces control through LCR power meter



CE RS-232 ☑ Handler ☑

Accessories / Fixtures

Standard

- Power Cord

- 0
- User Manual (CD)
- Ethernet cable
- Black thermoplastic sleeve (6210)
- Red thermoplastic sleeve (6210)
- F6210 (DIP)

ptional

- PC Link software
- F6220 (SMD)
- 6210/6220/6240 connect plate (short/long)
- BNC+BNC cable

Applications

Components: High current power inductor, common mode choke, mini molding choke, high power components of EV charging connector Electric Vehicles: Electric supercharger system

Specifications

DC Bias Model Name	6210	6220	6240	
Output Current			0.000A-40.000A	
	0.000A-10.000A 0.000A-20.000A 0.000A-40.000A 0.000A-1.000A 1%+5mA			
Accuracy	1.001A-5.000A 2%			
	5.001A-20.000A 3%			
Power Consumption	320W max. 640W max.			
LCR Meter /	520W max.		040W max.	
Impedance Analyzer	6632			
Frequency (Hz)	10-1/3/5/10/20/30M			
AC Drive Level	10mV-2Vrms			
DC Drive Level	1V (Fixed)			
Output Impedance	25 Ω, 100 Ω (switchable)			
Measurement Parameters and Ranges	R, X	±0.000mΩ-99	±0.000mΩ-9999.99MΩ	
	IYI	0.00000µS-999.999kS		
	G, B	\pm 0.00000 μ S-999.999kS		
	θRAD	\pm 0.00000-3.14159		
	θDEG	$\pm 0.000^{\circ}$ -180.000°		
	Cs, Cp	\pm 0.00000pF-9999.99F		
	Ls, Lp	\pm 0.00nH-9999.99kH		
	D	0.00000-9999.99		
	Q	0.00-9999.99		
	Δ	± 0.00 %-9999.99%		
	Rdc	0.00mΩ-99.9999MΩ		
	εr' εr"	0-100000		
	μr' μr"	0-100000		
Output Current (Max.)	60AMP/120AM	C	320AMP	
LCR+DC BIAS Frequency Response	100-3M 100-1M			
Constant Power Output		•		
Current Switch		•		
DC Resistance		•		
Current Graphic Scanning Analysis		•		
Frequency Graphic Scanning Analysis		•		
Temperature Rise		•		

General

Power Supply	Voltage 88-264Vac		
	Frequency 47-63Hz		
Interface	RS-232, Handler		
Trigger Test	Auto, Manual, RS-232, GPIB, Handler		
Environment	Temperature: 10-40 $^\circ \! \mathbb{C}$, Humidity: 20-90%RH		
Dimension (W*H*D)	337×145×525mm (6210/6220) 435×132×525mm (6240)		
Weight	15kg (6210/6220), 20kg (6240)		

Key Features



I sat (Magnetic saturation current curve)



The value of the inductance is 36.4uH.



Using a DC Bias current source to apply a 10A bias current to the inductor, the inductance decreased from 36.4uH to 2.65uH.



foil cracked due to high temperature

Magnetic saturation current is called I sat, and the temperature rise current is called I rms. When the transformer and the inductor pass a large current in the actual circuit operation, the magnetic field of the magnetic core will produce magnetic saturation, which will cause the inductance characteristic to decline. Therefore, the R&D engineer will set the current value of the inductance reduction allowable range.

B DC Bias Measurement Principle



The above figure is a diagram of a general LCR test instrument, and the figure below is a diagram after carrying DC bias current. In addition to superimposing the DC source required for the measurement, an isolation capacitor is added to isolate the DC flowing into the instrument.



Standard fixture F6210 for measuring inductance, optional fixture F6220 for measuring SMD inductance.